



SPECTROSCOPIC PERSONAL RADIATION DETECTOR

FLIR identiFINDER[®] R200

FLIR identiFINDER R200 instruments are rugged, pager-sized Spectroscopic Personal Radiation Detectors (SPRD). They provide full ANSI N42.32 Personal Radiation Detector (PRD) compliance and feature next-generation solid state detector read-out technology that delivers ANSI N42.48 SPRD compliance with nuclide identification. The R200-G detects and identifies gamma radiation and the R200-GN additionally provides neutron detection capability. Law enforcement agencies and first responders use the R200 during routine traffic stops or high visibility events and in mass transit or critical infrastructure entry control points. The OneTouch Reachback™ feature uses the latest advancements in Bluetooth® and web server technologies to provide large-scale situational awareness by alerting others before arriving on-scene. The clear user interface and simple data presentation common to all identiFINDER products allow the R200 to quickly integrate with existing operational protocols and reduce training burdens.

www.flir.com/R200



CONFIDENT, BELT-WORN GAMMA AND NEUTRON DETECTION

Outstanding spectral ability to enable fast front-line detection and response

- Fully ANSI N42.42 and ANSI N42.48 compliant for gamma identification performance
- Technologically advanced SiPM with CsI to provide <7.5% resolution
- Field-proven and trusted template matching algorithms shared with the rest of the identiFINDER line
- Two models available: gamma detection and ID (R200-G) and gamma detection and ID + neutron detection (R200-GN)



RUGGED, IP67 AND MIL-STD 810G RATED ENCLOSURE

Survives tough missions so you can wear with confidence

- IP67 rated for use in harsh environments or temporary submersion during decontamination
- MIL-STD 810G (salt/fog) compliant
- Weighs less than 1 lbs. and is 1.5m drop-tested on all six sides
- No user maintenance
- Automatic calibration and stabilization



EASY THREE-BUTTON CONTROL EMPOWERS OPERATOR

Low training burden for quick field adoption

- Easy to interpret results and interface designed to align with typical operating procedures
- Clear memory display outperforms competition in all lighting conditions
- OneTouch Reachback™ and intuitive mobile app provide large-scale situational awareness by allowing operators to send immediate notifications with the single push of a button

SPECIFICATIONS

identiFINDER R200 (G and GN models)

| | |
|---------------------------------|---|
| Technology | Spectroscopic personal radiation detector (SPRD) |
| Gamma (CsI) | (18mm) ³ Cesium Iodide (CsI) with Silicon Photomultiplier (SiPM) |
| Gamma/Neutron (ZnS) | 27 mm x 62 mm x 5 mm (GN model only) |
| Energy Range (Gamma) | 25 keV - 3 MeV |
| Gamma Spectrum | 1024 channels; 3 MeV |
| Gamma Sensitivity (Cs-137, CsI) | 3 cps/urem/h |
| Neutron Sensitivity | ≥ 2.6 cps/nv (GN model only) |
| Dose Rate / Accuracy (Cs-137) | ≤100 nSv/h – 250 μSv/h (≤10μRem/h – 25 mRem/h); ±20% |
| Typical Resolution | ≤7.5 % FWHM at 662 keV |
| Service Interval | Recommended five-year factory maintenance interval; annual dose rate calibration interval |

Sampling & Analysis

| | |
|----------------------|---|
| Sample Introduction | Absorption of EM gamma and neutron emissions |
| Threats | Detects gamma and neutron radiation emitted from natural occurrences in the environment, special nuclear material, industrial, or medical material |
| Standards Compliance | ANSI N42.32 PRD standard fully compliant ANSI N42.48 SPRD standard fully compliant, including nuclide identification ANSI N42.42 data format standard fully compliant |
| Sampling & Analysis | From a few seconds to minutes |

System Interface

| | |
|-----------------------|---|
| Display & Alerts | Memory LCD black and white display |
| Communication | USB 2.0; mini-B socket; Bluetooth® ≤10m range (removable) |
| Data Storage | 30MB internal memory; up to 5000 spectra |
| Training Requirements | <10 mins for operator; 1 day for advanced user |
| Connectivity | Online mobile app available (Android, iPhone) |
| Software | On-board webserver software |

Power

| | |
|---------------|---|
| Input Voltage | 100-240 VAC (wall and car adapters and USB cable supplied) |
| Battery Specs | Internal single cell Li-ion: operational battery life ≥36h; replaceable back-up CR-123A: operational battery life ≥18h; Recharge time ≤6h when using AC or USB power source |
| Startup Time | <2 mins from cold start |


Environmental

| | |
|------------------------|--|
| Operating Temperature | -22 to 122 °F (-30 to 50 °C) |
| Operating Humidity | 93% RH @ 35 °C non-condensing |
| Storage Temperature | 14 to 95 °F (-10 to 35 °C) |
| Enclosure & Protection | Plastic injection with rubber overmold; protection rating IP67 according to IEC 60529; MIL STD 810G (Salt Fog) compliant |


Physical Features

| | |
|------------------------|--|
| Dimensions (L x W x H) | 5.7 x 2.2 x 1.9 in (14.5 x 5.6 x 4.8 cm) |
| Weight | ≤0.88 lb (0.4 kg) |


Specifications are subject to change without notice.
For the most up-to-date specs, go to www.flir.com



Dose Rate Mode



Radioisotope Identification



Neutron Detection

HEADQUARTERS

FLIR Systems, Inc.
27700 SW Parkway Ave.
Wilsonville, OR 97070
USA

DETECTION SALES, AMERICAS

FLIR Systems, Inc.
1201 S. Joyce Street
Suite C006
Arlington, VA 22202
USA
PH: +1-877-692-2120

DETECTION SALES, APAC

FLIR Detection, Inc.
10 Kallang Avenue #09-10
Aperia Tower 2
Singapore 335910
PH: +65-6822-1596

DETECTION SALES, EMEA

FLIR Detection, Inc.
Luxemburgstraat 2
2321 Meer
Belgium
PH: +32 (0) 3665 5106

detection@flir.com

www.flir.com
NASDAQ: FLIR

Equipment described herein is subject to US export regulations and may require a license prior to export. Diversion contrary to US law is prohibited. Imagery for illustration purposes only. Specifications are subject to change without notice. ©2020 FLIR Systems, Inc. All rights reserved. Revised 05/19/20

20-0749-DET-DET-R200 Datasheet A4



The World's Sixth Sense®